

Frick Rotary Screw Compressor Unit-125 HP

Mfg:

Model:

Stock No. ASLC016.


Serial No.:

Frick Rotary Screw Compressor Unit. Model: RXB 50. S/N: S0273NFMCTHAA3. Frick Sales Order: 209503-21. Refrigerant: R-717, max speed 3600 rpm, max design pressure 300 psi. Rotary Screw Compressor, Model/Serial No. XJS120S0982D. Refrigerant: NH3/R22, vol. ratio: 2.2 : 5.0, max speed 3600 rpm, max design pressure 362 psig. 125 hp, 460 V, 3 phase, 60 hz, fla 153.7. Hours 89,169. (ACN300).

Note: the following pictures show the exact unit prior to removal.



Job NO:	SOP 3014245				
Drawing No.:	FKC-4125Y1031.5				
Volts:	460	Phase:	3	Hz:	60
H.P.:	125	FLA:	153.7	LRA:	
LARGEST H.P.:	125				



The following pictures show the unit removed and stored at our facility in Edinburg, TX



