

Waukesha/Cherry Burrell Centrifugal Pump

Mfg: Waukesha/ Cherry Burrell

Model: 2085

Stock No. ATE005.

Serial No. 14138 98

Waukesha/Cherry Burrell Centrifugal Pump. Model: 2085. S/N: 14138 98. Capacity: 140 gpm with 55 tdh. Impeller diameter: 7-1/2 in. Single mechanical seals. Baldor industrial motor 5 hp, 1725 rpm, 208-230/460 V, 15-13.2/6.6 amps, 60 Hz, 3 phase. 316L stainless steel volute, backplate, impeller, and shaft. Designed for heavy-duty, high-efficiency applications. Provides exceptional corrosion resistance. Its five-bladed impeller with deeper eye allows for improved inlet characteristics. Inlets: (1) 3 in. dia. Q-line fitting. Outlets: (1) 2-1/2 in. dia. Q-line fitting. Overall dimensions: 21-1/2 in. L x 14 in. W x 15 in. H.

