

## Mycom 6-Cylinder Reciprocating Compressor – 125 HP

Mfg: Mycom

Model: N6WB

Stock No: BDNP04

Serial No: 630332

Mycom 6-Cylinder Reciprocating Compressor. Model: N6WB. S/N: 630332. Capacity rating: 108 tons at 80 BHP using R-717(ammonia) with suction temperature of 20°F and condensing temperature of 120°F. Leak (Psig) HP: 313, LP: 185. HYD (Psig) HP: 470, LP: 470. Toshiba motor: 125 Hp, 1760 rpm, 230/460 V, 302/151 A, 60 Hz, 3 phase. Vilter Part Winding starter box, rated: 125 HP, 460V. Henry Technologies Ltd, heat exchanger: model: C0SM-16046-140. serial no: C250826A-1. Oil filter dimensions: 3 ft. straight wall x 1 ft. 3 in. dia. Overall dimensions: 7 ft. 7 in. L x 6 ft. W x 8 ft. H.





