

Permco Blower / Vacuum Pump with Silencer - 5 HP

Mfg: Permco, Inc.

Model: 3600 LH IN

Stock No: BDPC017.4

Serial No: JP40567 JR

Permco Blower / Vacuum Pump with Silencer - 5 HP. Model: 3600 LH IN. S/N: JP40567 JR. According to the spec sheet, this unit is capable of 145 CFM with 3.5 PSI differential pressure, 1850 RPM, 3.5 BHP. Data based on inlet conditions of 68F air at 14.7 PSIG. Also capable of 7 in. Hg vacuum at 140 CFM, 1850 RPM, 3.1 BHP. Permco claims that these blowers are fully interchangeable with parts from the Roots AF series. Baldor motor: 5 HP, 1155 RPM, 208-230/460V, 60 Hz, TEFC. Ports: 2.5 in. Overall dimensions: 46 in. Long x 29 in. Wide x 69 in. High.





BALDOR-RELANCE INDUSTRIAL MOTOR	
CAT. NO.	M3708T
SPEC.	37G813T922H1
HP	5
VOLTS	208-230/460
AMPS	16.3-15/7.5
R.P.M.	1155
FRAME	215T HZ 60 PH 3
SER. F.	1.15 CODE J DES A CLASS F
NEMA NOM. EFF.	87.5 % P.F. 72 %
RATING	40C AMB-CONT
CC	010A USABLE AT 208V A
BEARINGS	DE 6307 CODE 6206
ENCL.	TEFC SN F0709283705
BALDOR ELECTRIC CO. FT. SMITH, AR. MFG. IN U.S.A. # 1256	