

Morris Ice-Master Remote Ammonia Ice Maker – 15 tons

Mfg: Morris & Associates

Model: NIM-RA-15T

Stock No: BDPC675.25

Serial No: 370-382

Morris and Associates Ice-Master Remote Ammonia Ice Maker. Mode: NIM-RA-15T. Serial: 370-382. Ice Type: Nugget. Refrigerant type: remote ammonia. Nominal production rating: 15 tons per 24 hours. Production quantity depends on the refrigerant temperature at evaporator, water inlet temperature, etc. Freeze surface material: stainless steel tubes. Suction accumulator Model: SAA-12D-33L. Built 1981. Serial: SAA-360-1281. Nat'l Bd: 125. Max WP: 250 PSI at 200F. Shell thickness: 0.180 in. Head thickness: 0.187 in. Baldor Washdown Duty Motor: 1HP, 208-230/460V, 60Hz, 3.5-3.2/1.6A, 1725 RPM, Frame: 56C, SF: 1.15. Overall Dimensions: 15 ft. L x 2 ft. 8 in. W x 6 ft. 4 in. H (ACN870).





