

**(2) Sundyne Maso / Sine Positive Displacement Pump with Control Panel**

**Mfg: Sundyne Maso / Sine**

**Model: MR-125**

**Stock No: BMFM001.10**

**Serial No: 100461103, 100451103**

(2) Sundyne Maso / Sine Positive Displacement Pump with Control Panel. Model: MR-125. S/N's: 100461103, 100451103. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Maximum particulate size: .5 in. SEW-Eurodrive Motor, 1 hp, 1680 rpm, 230/460 V, 3.65/1.82 amps, 60 Hz, 3 phase. Euro-drive, rpm out: 166 (final). Inlets/outlets: 2-1/2 in. dia. S-line fittings. Typical applications: cheese, curd & whey, cottage cheese, fruit concentrates, syrups, beer, batter, frostings fillings, soups, stews, and chocolates. Overall dimensions: 3 ft. 3 in. L x 2 ft .6 in. W x 4 ft. H. (ACN79-pump,motor,Eurodrive only).







