

Pneumatic Alcoa Capper

Mfg:

Model: 212/8

Stock No. 250.BP14a

Serial No.

Pneumatic Alcoa Capper. Capacity: 400 BPM. Model 212/8. 8 Head. Set for 28 mm plastic caps. Center between heads: 4-1/2 in. Transmission: 3 hp, 220/460 V. Conveyor size 3-1/4 in. No transmission on conveyor. Overall dimensions: 68 in. L x 45 in. W x 93 in. H.



