

Fristam FL-II-75L Positive Displacement Pump

Mfg: Fristam

Model: FL275L

Stock No.: CAGC1014

Serial No.: 75L0802294 / 0688510006

Fristam Positive Displacement Pump. Model: FL2-75-L. Serial 75L0802294 / 0688510006. Max speed: 800 RPM. Max pressure: 120 PSI. Displacement per revolution: 0.098 gallons. Max flowrate: 78.4 GPM at 800 RPM. Gear ratio: 11.71 (150 final RPM). GE motor: 7.5 HP, 1755 RPM, 208-230/460V, 60 Hz, 3-phase. Ports: 2 in.



