

Sweco 48 in. Vibratory Shaker Model LS48S66

Mfg: Sweco

Model: LS48S66

Stock No. CCPF117.

Serial No. LS48-779-51

Sweco 48 in. Vibratory Shaker.

- Model LS48S66.
- S/N LS48-779-51.
- 316 Stainless steel.
- Vibrator consists of top plastic lid, two sifting levels, and bottom base.
 - First level inner dimensions: 45-1/2 in. dia. x 7 in. H, with (97) 2-1/2 in. dia. x 3/4 in. H. Plastic Rings atop fine mesh sifting screen. Underneath screen are (36) 6-Ring Honeycomb Plastic Pieces, 5 in. dia. x 3/4 in. H. Supported by a 47 in. dia. Screen with numerous 3/4 in. dia. openings.
 - Second level inner dimensions: 45-1/2 in. dia. x 7 in. H., downward sloping from center. Both levels are supported by (14) 2 in. dia. x 5-1/2 in. H. Springs and are clamped together.
- Vibrator Inlets/Outlets: (1) 3 in.
 - Lid Inlet, first level- (2) 8-1/4 in. dia.
 - Outlets, second level- (1) 8-1/4 in. dia.
- Outlet and (2) 6 in. dia. Side Openings.
- Motor Specifications: 2.5 hp, 1200 rpm, 3- phase.
- Overall Dimensions: 70 in. L x 54 in. W x 48 in. H.



