

Frick TDSH193S Rotary Screw Compressor

Mfg: Frick

Model: TDSH193S1484CR

Stock No: CFPH700A

Serial No: TDSH193S1484CR

Frick TDSH193S Rotary Screw Compressor. Model / S/N: TDSH193S1484CR. Refrigerant: NH3/R22. Compressor was removed from an RWBII 100 rotary screw compressor packages. Vol. ratio: 2.2-5.0. Max speed rpm: 4500. Max Design pressure: 362 psi/KPa 2500. Inlets: 5 in. suction. Outlet: 4 in. discharge. Approximate weight: 1,720 lbs. Overall dimensions: 4 ft. 8 in. L x 2 ft. W x 2 ft. 1 in. H.





FPICK
ROTARY SCREW COMPRESSOR
MODEL / SERIAL NO.
TDSH193S14040R

REFRIGERANT	NH3/R22
VOL. RATIO	2.2-5.0
MAX. SPEED RPM	4500
MAX. DESIGN PRESSURE	PSIG. 382
	kPa. 2600

COMP. PATENT
WAYNESBORO, VA 22988