

## Foxboro I/A Series Vortex Flowmeter Sensor

Mfg: Foxboro

Model: 83S-D03TNA

Stock No. CGMM356.3

Serial No. 00231580

Foxboro I/A Series Vortex Flowmeter Sensor. Model: 83S-D03TNA. S/N: 00231580. Maximum working pressure: 150 psi @ 100 °F. Ref. K-factor: 78.512 pulses/cu. ft. Max. ambient temp: 185 °F. Temp Limit: 350 °F. Digital display. Meter body mat'l: 316 SS. The I/A Series 83S-D is a high-performance vortex flowmeter designed for food and pharmaceutical sanitary liquid service and CIP (clean-in-place) systems. Overall dimensions: 7-1/4 in. L x 7 in. W x 12-1/2 in. H.



