

Supercharger Plate Heat Exchanger


Mfg: Supercharger

Model: UX-216-HP-95

Stock No. CJRP5270.6

Serial No. P21510H

Supercharger Plate Heat Exchanger. Model UX-216-HP-95. S/N: P21510H. Dwg. No: D-32804. (94) Plates. Heating surface area: 375.4 sq. ft. Plate pack dimensions: 12.43 in. (minimum), 13.37 in. (maximum). MAWP: 75 psi. Maximum temperature: 250 °F. Test pressure: 113 psig. Inlets/outlets: (2) 4 in. inlets/outlets with 9 in. dia. flanges and (8) 3/4 in. dia. holes at a center-to-center distance of 7-1/2 in., (2) 2 in. dia. inlets/outlets with 6 in. dia. flanges and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 5-3/4 in. Overall dimensions: 60 in. L x 23 in. W x 62 in. H.



NATIONAL BOARD NO. <u>NA</u>			
TEXAS DIVISION-TRANTRER INC. WICHITA FALLS, TEXAS			
<u>NA</u>	SUPERCHARGER	ITEM NO.	<u>3624</u>
MODEL <u>UX-216-HP-95</u>		MIN.	MAX.
SHOP ORDER NO. <u>32804</u>	PLATE PACK DIM. (INCHES)	<u>12.43</u>	<u>13.37</u>
SERIAL NO. <u>P21510H</u>	SURFACE AREA (SQ. FT.)	<u>375.4</u>	
MAX. ALLOW W.P. <u>75 PSI</u>	NET WEIGHT (LBS)	<u>4100</u>	
MAX. TEMP. <u>250 F</u>	TEST PRESS. (PSIG)	<u>113</u>	
YEAR BUILT <u>1970</u>	DRAWING NO.	<u>D-32804</u>	

