

Supercharger Plate Heat Exchanger


Mfg: Supercharger

Model: UX-216-HP-237

Stock No. CJRP5271.6

Serial No. P27622H

Supercharger Plate Heat Exchanger. Model: UX-216-HP-237. S/N: P27622H. Dwg. No: D64620. Number of stainless steel plates: 237. Heating surface area: 948.6 sq. ft. Plate pack dimensions: 31.00 in. (minimum), 33.36 in. (maximum). MAWP: 100 psi. Maximum temperature: 175 °F. Test pressure: 150 psig. Inlets/outlets: (2) 4 in. dia. inlets/outlets with 9 in. dia. flanges and (8) 3/4 in. dia. attachment holes at a center-to-center distance of 7-1/2 in., (2) 2 in. dia. inlets/outlets with 6 in. dia. flanges and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 5-3/4 in. Overall dimensions: 82 in. L x 30 3/4 in. W x 62 in. H.





CERTIFIED
BY TEXAS DIVISION - TRANTER INC.
WICHITA FALLS, TEXAS

ITEM NO. 7411

MODEL 17-915-HP-237

SHOP ORDER NO	8520	PLATE PACK DIM (INCHES)	MIN. MAX
SERIAL NO	275224	SURFACE AREA (SQ FT)	840.6
MAX. ALLOW W P	25000	NET WEIGHT (LBS)	8720
MAX. TEMP	700	TEST PRESS. (PSIG)	150
YEAR BUILT	1980	DRAWING NO.	8520W