

2006 Baltimore Aircoil Company 3000 Series Stainless Steel Cooling Tower – 240 Tons

Mfg: Baltimore Aircoil Company

Model: 3240A (JE240A-JM)


Stock No: CPEG501.65



Serial No: U070214501

2006 Baltimore Aircoil Company 3000 Series Cooling Tower. Model: 3240A (JE240A-JM). Serial No: U070214501. Nominal capacity rating: 240 tons with water flow of 720 gpm at respective entering and leaving water temperatures of 95°F and 85°F at a 78°F wet bulb temperature. All structural steel components are constructed of 304 stainless steel. Fan motor: US Motors, hostile duty, 7.5 hp, 1765 rpm, service factor: 1.15, 21.10 amps, inverter duty, 200v, 60 Hz, 3 phase. Listed shipping weight: 6790 lbs. Overall dimensions: 18 ft. 1/2 in. L x 8 ft. 6 in. W x 9 ft. 10 in. H.









Baltimore Aircoil Company P.O. BOX 7322
BALTIMORE, MD. 21227
(410) 799-6200

B.A.C. MODEL NO. JE240A-JM
SERIAL NO. U070214801
BELT NO. 28-3103

270047PA REV. L

MANUFACTURED UNDER ONE OR MORE PATENTS ISSUED IN THE

SPECIAL FEATURES B533059
COOLING TOWER DUTY
TEAO FPM AIR VEL 1000

CATALOG# HV47V2H MODEL# BY45
6206-2RSJCS 6206-2RSJCS
TYPE CONT ENCL TE
FR 219T ID# K12-BY45-N S49 002
PH 3 40°C CONT WT 160 LB BAL .08 IFS
INCL CLASS F DUTY CONT WT 160 SF 2.15 HZ 60
HP 7.50 RPM 1765 NEMA NON EFFICIENCY 93.7
VOLTS 200 MAX KW/HP 63.6 CODE H DES B
AMPS 21.10 PF 83.6 CODE H DES B
CUST P/N 22AJDAB6GA

NEMA MG1 PART 31		INVERTER DUTY		AMPS
TORQUE	HZ RANGE	MAX RPM		V
<u>22.3</u> LB-FT	<u>6.60</u>	<u>180-1800</u>	<u>22.2</u>	
POLE	FL SLIP	RPM	SF	1.0
ENCODER	PPR	INV. TYPE		

MADE IN MEXICO

Hostile Duty Inverter Suitable
NEMA Premium
VT & 4:1 CT