

Waukesha 60 Positive Displacement Pump

Mfg: Waukesha

Model: 060

Stock No: DBBP185414.17a

Serial No: 264646 00

Waukesha Positive Displacement Pump. Model: 060. Serial No: 264646 00. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 6-3/8 in. rotors. Mounted on stainless steel cart, with Baldor motor: 2 hp. 1725 rpm, 208-230/460 volts, 6.5-6.2/3.1 amps, 60 Hz, 3 phase, motor drive: 5.0 ratio, 1750/350 in/out rpm, 910 in/lb. 5.30 input hp. Reliance Electric Variable Frequency Drive (SP500), 2 hp. 380-460 input VAC, 380-460 output VAC. 4.2 and 3.4 amps. 50/60 Hz. 0-240 Hz. 3 phase (1) 2-1/2 in. S-line inlet. (1) 2-1/2 in. S-line outlet. Overall dimensions: 3 ft. 7-1/2 in. L. x 1 ft. 3-1/8 in. W. x 3 ft. 5 in. H.







