

Waukesha 15 Positive Displacement Pump

Mfg: Waukesha

Model: 015

Stock No: DBBP185424.11

Serial No: 173027 95

Waukesha Positive Displacement Pump. Model: 15. S/N: 173027 95. Flow rate for new pump is 9 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 3-1/4 in. rotors. Square D manual motor starting switch. Reliance electric X-V Motor drive size: B122, Assembly: 105, Belt: 605036-29-C. H.P. 1-1/2, Output speeds rpm max: 300 and the minimal 33.3 Gear ratio: 14.0. Reliance electric motor: hp not specified. 1725 rpm, 230/460 volts, 6.8/3.4 amps, 60 HZ, 3 phase. (1) 1-1/2 in. s-line inlet. (1) 1-1/2 in. s-line outlet. Overall dimensions: 3 ft. 7 in. L. x 1 ft. 3-1/4 in. W. x 2 ft. 11 in. H.(ACN60).







