

Mueller Insulated and Jacketed Stainless Steel Tank- 60 Gallon

Mfg: Mueller

Model: 60Gal-"F"

Stock No. DBBP2962.2

Serial No. T-20034

Mueller Insulated and Jacketed Stainless Steel Tank- 60 Gallon. Model: 60Gal-"F". S/N: T-20034. Inside dimensions: 21-1/2 in. x 38 in. L. MAWP @ 100 °F: 50 psi. Test pressure: 63 psi. Medium: 30% Glycol. Filter: 3-1/2 in. dia. x 25-1/2 in. H. Filter housing: 4 in. dia. x 27-1/2 in. H. 18 in. L x 11 in. W product tray. Inlets: (1) 1 in. dia. NPT (female, media), (1) 1 in. dia. sanitary fitting (product), (1) 3/8 in. dia. barb fitting (product 2). Outlets: (1) 1 in. dia. NPT (female, media), (1) 1 in. dia. sanitary fitting (tank), (1) 3/8 in. dia. barb fitting (product 2). (4) casters for easy positioning. Overall dimensions: 46 in. L x 27 in. W x 74 in. H.





