

Bell & Gossett Centrifugal Pump

Mfg: Bell & Gossett

Model: 60

Stock No. DBHK008.

Serial No. 931151RF

Bell & Gossett 60 Pump. S/N: 931151RF. Lesson motor: 3 - 4 hp, 1750 - 1425 rpm, 208-230/460 V, 2.8/3.0 - 1.4/1.5 FLA, 3 phase. Pump capacity: 10 gpm at 43 ft. head. Flange diameter: 4-1/2 in. with (2) holes, center to center: 3-1/2 in. Inlets/outlets: 2 in. Overall dimensions: 24 in. L x 10 in. W x 23 in. H.

