

Bell & Gossett Pump

Mfg: Bell & Gossett

Model: 153111/4BC87/8PF

Stock No. DBHK014.

Serial No. 900864

Bell & Gossett Pump. Model: 153111/4BC87/8PF. S/N: 900864. Unimount 125 motor, 3 hp, 1750 rpm, 230/460 V, 9.0/4.5 FLA, 10.5/5.25 SFA, 60 Hz, 3 phase. Pump capacity: 52.8 gpm at 82.5 ft. head. Maximum press: 175 psi. Inlets/outlets: (2) 2 in. female threaded. Overall dimensions: 24 in. L x 14 in. W x 20 in. H.

