

**Vilter 440 Series 8-Cylinder Reciprocating Compressor - 125 HP**

**Mfg: Vilter**

**Model: 448**

**Stock No.: DBPB208**

**Serial No.:**

Vilter 440 Series 8-Cylinder Reciprocating Compressor. Model: 448. Compressor nameplate is illegible. Lincoln electric motor: 125 HP, 1770 RPM, 460V, 60 Hz, 3-phase, 405T frame. Dimensions: 81 in. L x 48 in. W x 76 in. H. C-10





LINCOLN 		LINGGUARD®	
A.C. MOTOR®		DRIPPROOF	
SINGLE VOLTAGE MOTOR SUITABLE FOR 1/2 PART WINDING START		HP 125	RPM 1770
CONSULT INSTRUCTION MANUAL FOR 1/2 PART WINDING START CONNECTION INFORMATION		VOLTS 460	HERTZ 60
ACROSS THE LINE START CONNECTION		AMPS 144	PHASE 3
SERIAL U3960306300		TEMP. RISE 65 °C	TIME RATING CONT.
TV: TV4737A1		NEMA NOM. EFF. 93.6	NEMA MIN. EFF. 92.4
LINCOLN MIN. EFF. 92.5		LE CO. CODE	
THE LINCOLN ELECTRIC CO. CLEVELAND, OHIO U.S.A.		SERIAL U3960306300	

3-17055

VM

1 2 3  
7 8 9