

Vilter 440 Series 8-Cylinder Reciprocating Compressor - 125 HP

Mfg: Vilter

Model: 448

Stock No.: DBPC056

Serial No.: 32249

Vilter 440 Series Reciprocating Compressor. Model: 448. Serial 32249. Order: 78541. Size: A12K448V. Number of cylinders: 8. Displacement: 182 CFM. Nominal ratings: 94 TR at +20F / +95F (R-22 freon); 93 TR at +20F / +95F (R-717 ammonia). Lincoln Motor: 125 HP, 1770 RPM, 460V, 144 amps, 3-phase, 60 Hz, frame 405T. Compressor weight: 3400 lbs. Ports (suction/discharge): 4 in. / 3 in. Previously used with ammonia refrigerant.



