

APV Crepaco Stainless Steel Scraped Surface Heat Exchanger

Mfg: APV Crepaco

Model:

Stock No. DCBJ1021.5

Serial No. HP-1-264-S

APV Crepaco Stainless Steel Scraped Surface Heat Exchanger. S/N: HP-1-264-S. Jacketed cylinder: 6 in. diameter x 48 in. L. Rotating dasher. The product is pumped through the cylinder while the heating or cooling medium is circulated between the cylinder and the jacket. The machine is able to heat and cool fluids with particulates up to 1 in. (25.4 mm) and able to heat and cool high viscosity fluids. Reliance Electric Motor, 5 hp, 1155 rpm, 220/440 V, 15.2/7.6 amps, 60 cycles, 3 phase. Product inlet/outlet: 1-1/2 in. 'S' line. Overall dimensions: 87 in. L x 24-1/2 in. W x 49 in. H.



