

## 300 Gallon DCI Processor

- ▶ S/N 87-D-34799-A
- ▶ Inner dimensions: 42 in W x 54 in H slopped upto 58 in H
- ▶ Sloped Bottom, 2 in bottom outlet, 2 Thermowells
- ▶ 2-speed agitator, 1/2 to 1/4 HP, 460 Volt, 1800 RPM to 900 RPM
- ▶ 18-1/2 in manway, Top inlets (2) 1-1/2 in and (1) 3 in
- ▶ 1-1/2 in jacket connections, jkt rating 0 PSI
- ▶ Stainless Steel Ladder, 2 CIP spray balls

### Overall Dimensions

64 in W x 103 in H

---



DCI Processor 300 gallon

300 Gallon DCI Processor, S/N 87-D-34799-A, inner dimensions: 42 in. diameter x 54 in. H sloped up to 58 in. H, sloped bottom, 2 in. bottom outlet, 2 thermowells, 2-speed agitator, 1/2 to 1/4 hp, 460 volt, 1,800 rpm to 900 rpm, 18-1/2 in. manway, top inlets (2) 1-1/2 in. and (1) 3 in., 1-1/2 in. jacket connections, jkt rating 0 psi, stainless steel ladder, 2 CIP spray balls, overall dimensions 64 in. diameter x 103 in. H.



