

## 300 Gallon DCI Processor

- ▶ S/N 87-D-34799-B
- ▶ Inner dimensions: 42 in W x 54 in H sloped upto 58 in H
- ▶ Sloped Bottom, 2 in bottom outlet, 2 Thermowells
- ▶ 2-speed agitator, 1/2 to 1/4 HP, 460 Volt, 1800 RPM to 900 RPM
- ▶ 18-1/2 in manway, Top inlets (2) 1-1/2 in and (1) 3 in
- ▶ 1-1/2 in jacket connections, jkt rating 0 PSI
- ▶ Stainless Steel Ladder, 2 CIP spray balls

### Overall Dimensions

64 in W x 103 in H

---



4/2/2004





