

## Krack Low Temperature 4-Fan Blast Evaporator – 57 Tons

Mfg: Krack

Model: PCA4H-110-10-3-10-RBA-HGU-LH

Stock No: DFDT14.3a

Serial No: 383358C12

Krack Low Temperature 4-Fan Blast Evaporator. Model: PCA4H-110-10-3-10-RBA-HGU-LH. Serial No: 383358C12. Refrigerant: recirculated, bottom-feed R-717 (ammonia). Rated capacity: 650,000 BTUH, or 57 tons for a -30°F room with a coil temperature of -40°F. Air at 101,000 cfm. (4) 10 hp motors, 1750 rpm, 460V, 60 Hz, 3 phase. This unit has an all-aluminum coil and features hot gas coil and pan defrost. Pipe flow designates this as a “left-handed” unit. Approximate weight 4950 lbs. Overall dimensions: 22 ft. 11 in. L x 4 ft. 2 in. W x 7 ft. 6 in. H.

