

Unused 2002 Buffalo Pumps Can-O-Matic II Ammonia Pump

Mfg: Buffalo Pumps

Model: HCR Can-O-Matic II

Stock No: DNBA021a

Serial No: 02441284-001

Unused 2002 Buffalo Pumps Can-O-Matic II Ammonia Pump. Model: HCR Can-O-Matic II. Serial No.'s: 02441284-001. Size: 3x2x13. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Max psi: 400. Impeller diameter: 13 in. Motor: 10 hp, 1750 rpm, 460 V, 15.5 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 2 in. dia. flanged port. Overall dimensions: 2 ft. L x 2 ft. W x 2 ft. H.(ACN76a).





