

Stainless Steel Framed Belt Conveyor – 18 in. Wide

Mfg:

Model:

Stock No.: DNBA221

Serial No.:

Stainless Steel Framed Belt Conveyor. Conveyor dimensions: 5 ft. 3 in. L x 1 ft. 6 in. W. Sew-Eurodrive motor, 1 hp, 1700 rpm, 230/460 V, 3.70/1.85 amps, 60 Hz, 3 phase. Sew-Eurodrive, ratio: 32.62:1, rpm out: 52 (final), torque: 3000 lb-in. Infeed/exit height: 2 ft. 10 in. Overall dimensions: 5 ft. 3 in. L x 2 ft. 5-1/2 in. W x 2 ft. 10 in. H.



