

Reeves Vari-Drive Gear Head Motor- 10-HP

Mfg: Reeves

Model:

Stock No. DPF1104.a

Serial No.:

Reeves Vari-Drive Gear Head Motor- 10-HP. Reliance Electric motor, 10 hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Reliance Electric motor drive, size: B453, 10 hp, output speed: 68 rpm maximum, 8.63 rpm minimum. Shaft dimensions: 7-1/2 in. diameter. Overall dimensions: 65 in. L x 24 in. W x 49 in. H.

