

## Reeves Vari-Drive Gear Head Motor- 10 HP

Mfg: Reeves

Model:

Stock No. DPF1107.a

Serial No.:

Reeves Vari-Drive Gear Head Motor- 10 HP. Reliance Electric motor, 10 hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Reliance Electric motor drive, size: B442, 10 hp, output speed: 230 rpm maximum, 29 rpm minimum, 17.1 ratio. Shaft dimensions: 6-1/2 in. diameter. Inlets/outlets oil: (2) 1 in. threaded male. Overall dimensions: 65 in. L x 25 in. W x 43 in. H.

