

Vilter Reciprocating Compressor, Size 446

Mfg: Vilter

Model: 446

Stock No. DPFI428.3

Serial No.

Vilter Reciprocating Compressor. Model: 446. 6 cylinders. Displacement at maximum rpm: 232 cu. ft./min. General Electric Motor, 75 hp, 1,770 rpm, 440 V, 91 amps, 60 cycles, 3 phase. Inlets/outlets: (2) 3 in. dia. pipes. Overall dimensions: 78 in. L x 48 in. W x 65 in. H. Penn Cut In/Out Oil controls.

