

Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX3451-235

Stock No: DPLS150.3

Serial No: FPX3451963635

Fristam FPX-Series Centrifugal Pump. Model: FPX3451-235. S/N: FPX3451963635. Flow rate for new pump is 125 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller: 9 in. diameter. Baldor Electric motor. 5 hp, 1760 rpm, 230/460 V, 13.6/6.8 A, 60 Hz, 3 phase. Inlet/outlet: (1) 3 in. S-line. (1) 2 in. S-line. (1) 3/8 in. port. Stainless Steel cart for maneuverability. Overall dimensions: 3 ft. L x 1 ft. 5 in. W x 3 ft. 2-5/8 in. H.





