

Hosokawa Bepex Rietz Stainless Steel Jacketed Blender

Mfg: Hosokawa Bepex

Model: RS-15-K3203-6

Stock No. DSBI091.34

Serial No. RS-780080

Hosokawa Bepex Rietz Stainless Steel Jacketed Blender. Approximately 13.85 cu. ft. product area to bottom of trough (100gallon product capacity) Model: RS-15-K3203-6. S/N: RS-780080. Nat'l Bd: 42. 316 stainless steel. Jacket pressure at 274 °F: 30 psi. Trough metal thickness: 0.135. Jacket metal thickness: 0.135. Head metal thickness: 0.25/0.375. Product inlet: 42 in. L x 30-1/2 in. W with removable hinged lid. (2) Screw augers: 14 in. dia. x 41 in. L. 15 in. dia. housing, for blending. (2) Discharge outlets: 11-1/2 in. W x 4-1/2 in. H (oval). Discharge outlet covers are shut by pneumatic cylinders. (2) Sterling Motors: 3 hp, 1735 rpm, 230/460 V, 8.5/4.3 amps, 60 Hz, 3 phase. (2) Dodge Motor Drives: 24.92 ratio, 69.62 rpm (final). Inlets/outlets: (1) 3/4 in. dia. threaded fitting, (1) 3/4 in. dia. pipe, (1) 3/4 in. dia. male ferrule with hex nut. Overall dimensions: 74 in. L x 53 in. W x 54 in. H.



