

Seward Stomacher Shredder

Mfg: Seward Stomacher

Model: 3500

Stock No. DSBI094.a

Serial No. 38125

Seward Stomacher Shredder. Model 3500. S/N 38125. Set times: continuous, 30 sec, 60 sec, 120 sec. Set speeds: low, normal, high. Electrical requirements: 110 V, 60 Hz, rated load 120 W. Stomacher paddles: (2) 8 in. L x 7 in. W. Rubber diaphragm: 24 in. L x 16-1/2 in. W. Overall dimensions: 19-1/2 in. L x 19-1/2 in. W x 16 in. H.

The high capacity 3500 has been specifically developed for operations that require the blending of larger volumes. It has a gentler action than the 80 and 400 models and is therefore better suited for blending powders and pathological samples.

The 3500 is particularly applicable to the extreme needs of specialist users including the water industry, pork processors and chocolate manufacturers. It is widely used in hospital departments such as clinical chemistry, gynaecology and geriatric food processing, and also in many industrial operations. The high capacity 3500 can handle samples from 1000 to 3500 mls.

