

Goulds Submersible Sump Pump

Mfg: Goulds

Model: WP1034-02

Stock No. DSLP038.2

Serial No. 118

Goulds Submersible Sump Pump. Model: WP1034-02. S/N: 118. Impeller diameter: 6 in. Motor, 1 hp, 460 V, 2.1 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. FNPT fittings. Overall dimensions: 17 in. L x 13 in. W x 16-1/2 in. H.



