

Nickell Co. Shell and Tube Heat Exchanger

Mfg: Nickell Co.

Model:

Stock No. DTTC026.

Serial No.:

Nickell Co. Shell and Tube Heat Exchanger. Natd Bd: 28373. Matd constr: carbon steel. Number of tubes: 120. Tube dimensions: 1 in. dia. x 12 ft.-1/2 in. L. Heat transfer surface area: approx. 378 sq. ft. Maximum working pressure: 250 psi. Maximum temperature: 300 °F. Minimum temperature: -20 °F. Inlets: (1) 4 in. dia port, (1) 2-1/2 in. dia. port, (1) 3 in. dia. port. Outlets: (1) 2-1/2 in. dia. port. Overall dimensions: 12 ft. 4 in. L x 2 ft. W x 3 ft. 9 in. H.



