

1993 Aurora/Hydromatic Self-Priming Sewage and Trash Pump

Mfg: Aurora / Hydromatic Pumps, Inc.

Model: 40MP

Stock No. DTTC2045.

Serial No. P3240

1993 Aurora / Hydromatic Self-Priming Sewage and Trash Pump. Model: 40MP. S/N: P3240. Capacity: 500 gpm @ 68 head feet (~30 psi using specific gravity of water = 1). Impeller: 9-5/32 in., two-vane, semi enclosed, grade 64-45-15 ductile iron. Seal option: carbon/ceramic, Type 21, SF1 C1. Buna N O-rings. B.C: CH. Baldor Industrial Motor, 15 hp, 1760 rpm, 230/460 V, 38/19 amps, 60 Hz, 3 phase. Heavy duty ball-type bearings. 4140 stress proof steel Pump Shaft, 316 stainless steel shaft sleeve. Inlets: (1) 3/4 in. dia. FNPT, (1) 4 in. dia. flanged port. Outlets: (1) 4 in. dia. flanged port. Overall dimensions: 5 ft. 3 in. L x 1 ft. 8 in. W x 3 ft. 4 in. H.

