

Ingersoll-Dresser Centrifugal Pump

Mfg: Ingersoll-Dresser

Model: D-824

Stock No.: DTTC2046

Serial No.: W8326

Ingersoll-Dresser Centrifugal Pump. Model: D-824. S/N: W8326. Size: 3x1.5x8. Flow rate for new pump is 140 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 7 in. Maximum impeller size: 8 in. Pump mat'l: Cl. Baldor industrial motor, 10 hp, 3450 rpm, 230/460 V, 24/12 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 1-1/2 in. dia. flanged port. Overall dimensions: 2 ft. 1 in. L x 1 ft. 6 in. W x 1 ft. 7 in. H. (ACN34)



