

Vilter 8-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: 448

Stock No.: DTTC840B

Serial No.:

Vilter 8-Cylinder Reciprocating Compressor. Model: 448. Last used with R-717 producing 93 tons at 105 bhp with a 20°F suction temperature and a 96.2°F condensing temperature. Displacement: 182 cfm. Maximum speed: 1,200 rpm. Maximum discharge temperature: 300°F. Liquid-cooled heads. Inlets: (1) 3/4 in. dia. pipe (liquid), (1) 4 in. dia. refrigerant suction port. Outlets: (1) 3/4 in. dia. pipe (liquid), (1) 3 in. dia. refrigerant discharge port. Overall dimensions: 4 ft. L x 3 ft. 4 in. W x 5 ft. 11 in. H.(ACN233).

