

## Thermal Care/Mayer Water-Cooled Accuchiller- 5 Ton

Mfg: Thermal Care/Mayer

Model: AQ0W0504

Stock No. DTWA200.1a

Serial No. 541500100C6

Thermal Care/Mayer Water-Cooled Accuchiller- 5 Ton. Model: AQ0W0504. S/N: 541500100C6. Refrigerant: R-22. Heat transfer fluid: Glycol. Minimum/Maximum temperature: 30/60 °F. System requirements: 460 V, 14 FLA, 60 Hz, 3 phase. Copeland Scroll Compressor, Model: CRN5-0500-TFD-274, S/N: 99L11797B. Thermal Care/Mayer Motorpump, Model: 12B, size: 1.25x1, 1-1/2 hp, 60 Hz, 3 phase. Accuchiller series AQ are built for quiet performance, nonferrous construction. Its microprocessor controller provides diagnostics, easy operation and accurate temperature control. Inlets: (1) 1 in. dia. NPT (male, from process), (1) 1 in. dia. NPT (female, condenser). Outlets: (1) 1 in. dia. bevel with hex (female, to process), (1) 1 in. dia. NPT (female, condenser). Overall dimensions: 38 in. L x 27 in. W x 37 in. H.





