

Blodgett Over/Under Electric Oven

Mfg: Blodgett

Model: FA-100

Stock No. DTWA203.2a

Serial No. 268FA-7

Blodgett Over/Under Electric Oven. Model: FA-100. S/N: 268FA-7. Stainless steel. Natural gas fueled oven. Rated input: 1-1/4 hp (42500 BTU/hr). System requirements: 115 V, 11.3 amps, 60 Hz, single phase. Century Blower Motor: 3/4 hp, 1725 rpm, 115 V, 9.6 amps, single phase. General Electric Blower Motor: 3/4 hp, 1725 rpm, 115/2230 V, 13.4/6.7 SFA, 12/6.0 amps, 60 Hz, single phase. Two oven units inside dimensions: 29 in. L x 21 in. W x 20 in. H. Five chrome plated racks. Control system switches: blower on/off, burner on/off, oven temperature control, and 0-60 minute timer. Overall dimensions: 41 in. L x 38 in. W x 70 in. H.



