

## Steel Accumulation Table/Conveyor

Mfg:

Model:

Stock No. DTWA353L.

Serial No.:

Steel Accumulation Table/Conveyor. Belt width (accumulation): 47 in. Belt width (transfer): 7-1/2 in. Maximum aperture/clearance above belt: 5 in. W x (2 to 10 in. H). Reliance Electric Motor, 3/4 hp, 1725 rpm, 208-230/460-480 V, 2.9-2.6/1.3-1.5 amps, 60 Hz, 3 phase. Reliance Electric Gear Reducer, 90 ratio, 19 rpm (final). Reliance Electric Motor, 1/2 hp, 1725 rpm, 208-230/460-480 V, 2.4-2./1.2-1.4 amps, 60 Hz, 3 phase. Motor drive. Infeed/exit height: 35 in. Overall dimensions: 15 ft. 10 in. L x 65-1/2 in. W x 37-1/2 in. H.



