

## Labour Taber Pump

**Mfg: Labour Pump Co.**

**Model: DPL**

**Stock No: DTWA506**

**Serial No: L25544**

Labour Taber Pump. Model: DPL. S/N: L25544. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum speed: 1750 rpm. Size: 15. Impeller diameter: 8-3/8 in. Dayton Tri-Volt motor: 10 hp, 1750 rpm, 208-230/460 volts, 28.6-26.2/13.1 amps, 60 HZ, 3 phase. Inputs/Outputs: (1) 2-5/8 in. flange inlet dia. 4 mounting holes with 3/4 in. dia. 4 in. adjacent and 5-1/2 in. opposite. (1) 2-5/8 in. flange outlet dia. 4 mounting holes with 3/4 in. dia. 4 in. adjacent and 5-1/2 in. opposite. Overall dimensions: 4 ft. 1 in. L. x 1 ft. 2-1/2 in. W. x 2 ft. 8-1/2 in. H.





