

Stainless Steel Belt Blancher - 2 ft. Wide

Mfg:

Model:

Stock No.: DWKN208.60

Serial No.:

Stainless Steel Belt Blancher - 2 ft. Wide. Chain link belt width: 2 ft. Rod diameter: 0.270 in. Rod pitch: 1-1/2 in. Wire thickness: 0.026 in. Gap: 0.095 in. Maximum aperture/clearance above belt: 2 ft. W x 6-1/2 in. H. Cleat height: 4 in. Conveyor infeed height: 4 ft. Conveyor exit height: 6 ft. 10 in. Steam chamber length: 12 ft. Cooling chamber length: 8 ft. 6 in. Reliance Electric Motor, 1-1/2 hp, 1725 rpm, 208-230/460 V, 5.6/2.8 amps, 60 Hz, 3 phase. Boston Speed Reducer. Taylor Industrial Companies Line-E-Aire Pneumatic Control Valve, range: 3-15 psi, body rating: 150 psi. Inlets: (1) 3/4 in. dia. FNPT (media), (6) 1 in. dia. FNPT ports (sprayers), (1) 2 ft. W x 8 in. H infeed. Outlets: (4) 2 in. dia. FNPT (overflow), (1) 3 in. dia. FNPT (drain), (2) 6 in. dia. ports (drain), (1) 1 ft. 6 in. dia. port (exhaust). Overall dimensions: 31 ft. L x 5 ft. 1 in. W x 8 ft. 6 in. H.













