

Waukesha 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No.: DWKN218

Serial No.: 2026 SS

Waukesha 60 Positive Displacement Pump. Model: 60. S/N: 2026 SS. Flow rate for new pump is 90 gpm with required horsepower. Approximate current capacity with drive: 29 gpm. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Temperature range: -40°F to 300°F. 316 stainless steel body, cover and shaft. Seal option: O-rings. U.S Electrical Varidyne Syncrogear Motor, 2 hp, 1796 rpm, 420 V, 3.7 amps, 0 Hz, 3 phase. Syncrogear Speed Reducer, ratio: 9.45, rpm out: 190(final). Inlets/outlets: (2) 2-1/2 in. dia. ACME fittings. Overall dimensions: 3 ft. 3 in. L x 1 ft. 3 in. W x 1 ft. 3 in. H. (ACN102).





