

## Walker Stainless Jacketed Process Tank- 200 Gallon

Mfg: Walker

Model: PZ-CB

Stock No.EECA003.

Serial No. 2443

Walker Stainless Jacketed Process Tank- 200 Gallon. Model: PZ-CB. S/N: 2443. Nat'l Bd: 647. 304 stainless steel construction. Side sweep, bottom scrape agitator. Bottom dimpled jacket with spiral steam coil sidewall. Jacket MAWP @ 325 °F: 75 psig. Shell MAWP @ 325 °F: atm. Cone bottom. Sew-Eurodrive Motor, 1.21 hp, 1700 rpm, 208 V, 5.86 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Reducer, 25 rpm final, 3025 lb-in. Applications include: heating, cooling, mixing, blending, storing and batch processing. Inlets: (2) 1/2 in. dia. thermowell fittings, (1) 1-1/4 in. dia. FNPT (coil), (1) 1-1/4 in. dia. FNPT (dimple), (2) 3 in. dia. S-line fittings, (1) 10 in. dia. S-line fitting. Outlets: (1) 1/2 in. dia. port (sample), (1) 1-1/4 in. dia. FNPT (coil), (1) 1-1/4 in. dia. FNPT (dimple), (1) 4 in. dia. I-line fitting (discharge). Overall dimensions: 71 in. L x 58-1/2 in. W x 92 in. H.





