

Ingersoll-Rand Inc. Ace Closed Loop Fluid Cooler- 115 Ton

Mfg: Ingersoll-Rand Inc.

Model: ACE1000E2

Stock No. EECA006.

Serial No.

Ingersoll-Rand Inc. Ace Closed Loop Fluid Cooler- 115 Ton. Model: ACE1000E2. Elevation 2000 ft. Capacity: 1414740 btu/hr @ 50 % EG. Entering fluid temperature: 106.9°F. Leaving fluid temperature: 85°F. Evapco Centrifugal Pump, capacity: 152 gpm of 40% Ethylene Glycol, 5.19 in. impeller. U.S. Motor, 1-1/2 hp, 1730 rpm, 208-230/460 V, 5.0/2.5 amps, 60 Hz, 3 phase. (1) US Centrifugal Fan Motor, 15 hp, 1765rpm, 208-230/460 V, 43.3-39.2/19 amps, 60 Hz, 3 phase. Fluid cooler has (2) 4 in w threaded female connection Inlet/Outlet for product. Inlet: (1) 2 in port for water. Overall dimensions: 161 in. L x 75 in. W x 101 in. H.



