

**Safeline, Inc. / Mettler Toledo Metal Detector and Conveyor**

**Mfg: Safeline, Inc. / Mettler Toledo**

**Model: Powerphase 6 x 12**


**Stock No: EMRW005**


**Serial No: 43316**

Safeline, Inc. / Mettler Toledo Metal Detector and Conveyor. Model: Powerphase 6 x 12. S/N: 43316. Module serial no: 72473. Hardware version: V3c1. Firmware version: XT 1.02. Aperture/product clearance: 6 in. W x 11-3/4 in. H. Product clearance above the conveyor belt: 10 in. Hard plastic belt: 11 ft. 3 in. x 4 in. W (usable belt dimensions: 5 ft. 4 in. L x 4 in. W). Initial sensor capacities: 1.2 mm ferrous, 1.2 mm non-ferrous, 1.5 mm stainless steel. Safeline, Inc. control Initial box. Mod: SLP-30-B. Electrical ratings: 100-240 VAC, 5060 Hz, 1A. Overall control box dimensions: 9-1/2 in. L x 5-1/2 in. W x 11-1/2 in. H. Metal detector dimensions: 2 ft. 1 in. L x 11 in. W x 1 ft. 8-1/2 in. H. Overall detector and conveyor dimensions: 5 ft. 4 in. L x 2 ft. 5-1/2 in. W x 3 ft. 11-1/4 in. H.









MODULE SER No. <b>72473</b>	FREQUENCY	
STANDARD MODULE	800	300 / 800
REJECT CONFIRMATION	600	400 / 800
FAST RECOVERY	300	200 / 300
SLOW SPEED	100	100 / 300
FERRIOUS IN POGL	25	25 / 100
ENS	180° KEY PANEL	STAG FREQ <b>3</b>
PCB	4WIRE RS232 S/S P	
HARDWARE VERSION	<b>VX1</b>	
FIRMWARE VERSION	<b>X11-C8</b>	
SPECIAL		

WARNING: If a module replacement is necessary the frequency and options must be the same as the original module.  
 IF IN DOUBT, CONTACT YOUR SUPPLIER

**ELECTRIC, INC.**  
 IRVINE, CA 1-800-654-6220

MODEL NO. <b>SBY054NCA</b>	VOLTS <b>200/460V</b>		AMP. <b>1.70-1.62/0.81</b>
HP <b>1/2</b>	ENCL.	TENV	FRAME NO. <b>56C</b>
F/L RPM <b>1730</b>	MAX. AMB. <b>40 °C</b>	SERVICE FACTOR <b>1.15</b>	
INS. <b>F</b>	TIME RATING CONT.	BRG D.E. <b>6205</b>	NO. O.D.E. <b>6204</b>
3-PHASE	KVA CODE <b>K</b>	NEMA DESIGN <b>B</b>	
Hz <b>60</b>	EFFICIENCY <b>78.0%</b>		

LOW VOLTS	HIGH VOLTS
4 5 6	4 5 6
7 8 9	7 8 9
10 11 12	10 11 12

MADE IN KOREA

MFG DATE: JUN. 2000      S/N: **016335**