

Lowara / Goulds Pumps, Inc. Vertical Multi-Stage Pump

Mfg: Lowara / Goulds Pumps, Inc.

Model: SSV

Stock No: EMRW006

Serial No: 19429553

Lowara / Goulds Pumps, Inc. Vertical Multi-Stage Pump. Model: SSV. S/N: 19429553. Catalog number: 3SVCK13T. Nominal flow rate 60 gpm. Material of construction: 304 stainless steel. Operating temperature range: -20°F to 250°F. Maximum PSI: 360. Baldor Industrial motor: 15 hp, 3450 rpm, 208-230/460 v, 38-34/17 a, 60 Hz, 3 phase. (1) Electromate enclosures control box. (2) Jamesbury Corp. actuators: 120V, 1.0 a, 60 Hz. Inlets/outlets: (3) 1 in. ports, (1) 1-5/8 in. port. Multiple uses are provided by this series of pumps such as circulating hot or cold water for HVAC, water without suspended solids, pressure boosting, boiler feeds, applications with glycol, irrigation, R/O, and washers. Features and benefits include a simplified design for maximum reliability and faster repair, and ANSI flanges with the discharge above the suction. Impeller spacing is automatic for quick installation, reduced wear, and impeller O-ring seals produce high pressure and efficiency per stage to keep energy costs down. Overall dimensions: 3 ft. 3 in. L x 2 ft. 6 in. W x 4 ft. 6-1/4 in. H.







