

## Crepaco R3R Positive Displacement Pump

Mfg: Crepaco

Model: R3R

Stock No. ERCS004.

Serial No. A-7989

Crepaco R3R Positive Displacement Pump. Model: R3R. S/N: A-7989. Capacity: 9.50 gpm. Displacement per 100 revolutions: 1.50 gpm. Maximum capacity: 36 gpm. Maximum speed: 900 rpm. Toshiba Motor, 2 hp, 1720 rpm, 633 rpm (final), 230/460 V, 5.8/2.9 amps, 60 Hz, 3 phase. 3-A sanitary rated. Crepaco pumps are known for their rugged, long-lasting, efficient performance. Every pump in the line has as standard a stainless steel body, resilient molded rotors, and a heavy cast iron gear case, which provides long-lasting, economical service over a wide range of products and applications, easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages, dough, chocolate and shampoo. Inlets/outlets: (2) 1-1/2 in. dia. ACME fittings. Overall dimensions: 27 in. L x 13-1/2 in. W x 17-1/2 in. H.



