

Jayhawk Mustard Mill – 7.5 HP

Mfg: Jayhawk

Model: 2MPYC

Stock No.: FHF293b

Serial No.: B233

Jayhawk Mustard Mill. Model: 2MPYC. Serial: B233. Capacity: 75 GPH / 635 lbs. per hour. Century Motor, 7.5 hp, 3470/2890 rpm, 220-440 V, 60/50 cycle, 3 phase. The Jayhawk mustard mill is a wet process, stone grinding size reduction mill using precision balanced, diamond cut stones in varieties of applications to include mustard, hot sauce processing, or anything that requires reduction by wet grinding. Inlet: 1 in. bevel seat. Outlets: (1) 4 in. L x 1 in. W discharge. Overall dimensions: 27 in. L. x 15 in. W. x 16 in. H.





